

FVR38-38N Cut Sheet



NITRA pneumatic push-to-connect fitting, elbow flow control valve, rotating, meter-in, thermoplastic (PBT) body, nickel-plated brass threads, (1) 3/8in male NPT to (1) 3/8in push-to-connect. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FVR38-38N>

Technical Specifications

Brand	NITRA	Thread Material	Nickel-plated brass
Item	Fitting	Thread Sealant	Yes
Working Fluid	Air or inert gas	Fitting Measurement Type	SAE
Fitting Connection Type	Push-to-connect	Connection	(1) 3/8in male NPT and (1) 3/8in push-to-connect
Fitting Type	Elbow flow control valve	Operating Pressure	-29.5in Hg to 150 psi
Fitting Function	Rotating	Operating Temperature	32 to 140 deg F
Valve Function	Meter-in	Quantity per Pack	2
Body Material	Thermoplastic (PBT)	For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FVR38-38N.pdf>
See store item page for other formats.