

FVR8M-38G Cut Sheet



NITRA pneumatic push-to-connect fitting, elbow flow control valve, rotating, meter-in, thermoplastic (PBT) body, nickel-plated brass threads, 5/16in (8mm) tube to G3/8 BSPP connection(s). Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FVR8M-38G>

Technical Specifications

Brand	NITRA
Item	Pneumatic Push-to-connect Fitting
Fitting Type	Elbow flow control valve
Fitting Function	Rotating
Valve Function	Meter-in
Body Material	Thermoplastic (PBT)
Thread Material	Nickel-plated brass
Thread Sealant	Yes
Connection	5/16in (8mm) push-to-connect and G3/8 BSPP
Operating Pressure	-29.5in Hg to 150 psi
Operating Temperature	32 to 140 deg F
Quantity per Pack	2
For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document