

FVS4M-M5 Cut Sheet



NITRA pneumatic push-to-connect fitting, elbow flow control valve, rotating, meter-out, thermoplastic (PBT) body, nickel-plated brass threads, 5/32in (4mm) tube to M5 X 0.8 threaded connection(s). Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FVS4M-M5>

Technical Specifications

| | |
|------------------------------|--|
| Brand | NITRA |
| Item | Pneumatic Push-to-connect Fitting |
| Fitting Type | Elbow flow control valve |
| Fitting Function | Rotating |
| Valve Function | Meter-out |
| Body Material | Thermoplastic (PBT) |
| Thread Material | Nickel-plated brass |
| Thread Sealant | Yes |
| Connection | 5/32in (4mm) push-to-connect and M5 x 0.8 threaded |
| Operating Pressure | -29.5in Hg to 150 psi |
| Operating Temperature | 32 to 140 deg F |
| Quantity per Pack | 2 |
| For Use With | Flexible pneumatic tubing |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |