

# FVS6M-14R-B Cut Sheet



NITRA pneumatic push-to-connect fitting, elbow flow control valve, rotating, meter-out, nickel-plated brass body, nickel-plated brass threads, (1) R1/4 male BSPT to (1) 6mm push-to-connect. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FVS6M-14R-B>

## Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Type	Elbow flow control valve
Fitting Function	Rotating
Valve Function	Meter-out
Body Material	Nickel-plated brass

Thread Material	Nickel-plated brass
Thread Sealant	Yes
Fitting Measurement Type	Metric and SAE
Connection	(1) R1/4 male BSPT and (1) 6mm push-to-connect
Operating Pressure	0 to 300 psi
Operating Temperature	0 to 175 deg F
Quantity per Pack	2
For Use With	Flexible pneumatic tubing

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/FVS6M-14R-B.pdf>  
See store item page for other formats.