

# FVS6M-38G Cut Sheet



NITRA pneumatic push-to-connect fitting, elbow flow control valve, rotating, meter-out, thermoplastic (PBT) body, nickel-plated brass threads, 6mm tube to G3/8 BSPP connection(s). Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FVS6M-38G>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Pneumatic Push-to-connect Fitting
<b>Fitting Type</b>	Elbow flow control valve
<b>Fitting Function</b>	Rotating
<b>Valve Function</b>	Meter-out
<b>Body Material</b>	Thermoplastic (PBT)
<b>Thread Material</b>	Nickel-plated brass
<b>Thread Sealant</b>	Yes
<b>Connection</b>	6mm push-to-connect and G3/8 BSPP
<b>Operating Pressure</b>	-29.5in Hg to 150 psi
<b>Operating Temperature</b>	32 to 140 deg F
<b>Quantity per Pack</b>	2
<b>For Use With</b>	Flexible pneumatic tubing

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>