

# FXCS-0B30GLD Cut Sheet



Killark control station cover assembly, hazardous location rated, factory sealed, two pilot lights, indicating light, green/green, 110 VAC/VDC LED, green, operator only, (2) blank legend plate(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FXCS-0B30GLD>

## Technical Specifications

|                                      |                                |
|--------------------------------------|--------------------------------|
| <b>Brand</b>                         | Killark                        |
| <b>Item</b>                          | Control station cover assembly |
| <b>Application</b>                   | Hazardous location rated       |
| <b>Factory Sealed</b>                | Yes                            |
| <b>Housing Material</b>              | Aluminum                       |
| <b>Control Station Configuration</b> | Two pilot lights               |
| <b>Operator Type</b>                 | Indicating light               |
| <b>Operator Color</b>                | Green/green                    |
| <b>Indicator</b>                     | 110 VAC/VDC LED                |
| <b>Light Color(s)</b>                | Green                          |
| <b>Contact Type</b>                  | Operator only                  |
| <b>Legend Plate Type</b>             | (2) blank                      |
| <b>NEMA Rating</b>                   | 3/7/9                          |
| <b>Requires</b>                      | FXB series splice/device box   |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E53360                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | E12379                                 |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | LR11714                                |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |