

FXCS-0K2L3F22A Cut Sheet



Killark control station cover assembly, hazardous location rated, factory sealed, single selector switch, key-operated, 2-position, black, spring return from right, (1) N.O./ (1) N.C. contact(s), legend plate marking "OFF ON".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FXCS-0K2L3F22A>

Technical Specifications

| | |
|--------------------------------------|--------------------------------|
| Brand | Killark |
| Item | Control station cover assembly |
| Application | Hazardous location rated |
| Factory Sealed | Yes |
| Housing Material | Aluminum |
| Control Station Configuration | Single selector switch |
| Number Of Positions | 2 |
| Key Removable Position | Key removable left position |
| Operator Type | Key-operated |
| Operator Color | Black |
| Action | Spring return from right |
| Contact Type | (1) N.O./ (1) N.C. |
| Legend Plate Marking | OFF ON |
| NEMA Rating | 3/7/9 |
| Requires | FXB series splice/device box |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E53360 |
| UL Recognized File # | None |
| UL Hazardous File # | E12379 |
| CE | None |
| CSA File # | LR11714 |
| RoHS Status | No |
| EU REACH | View EU REACH document |