

FXCS-0K2L3F22A Cut Sheet



Killark control station cover assembly, hazardous location rated, factory sealed, single selector switch, key-operated, 2-position, black, spring return from right, (1) N.O./ (1) N.C. contact(s), legend plate marking "OFF ON".

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FXCS-0K2L3F22A>

Technical Specifications

Brand	Killark
Item	Control station cover assembly
Application	Hazardous location rated
Factory Sealed	Yes
Housing Material	Aluminum
Control Station Configuration	Single selector switch
Number Of Positions	2
Key Removable Position	Key removable left position

Operator Type	Key-operated
Operator Color	Black
Action	Spring return from right
Contact Type	(1) N.O./ (1) N.C.
Legend Plate Marking	OFF ON
NEMA Rating	3/7/9
Requires	FXB series splice/device box

Agency Approvals

UL Listed File #	E53360
UL Recognized File #	None
UL Hazardous File #	E12379
CE	None
CSA File #	LR11714
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/FXCS-0K2L3F22A.pdf>
See store item page for other formats.