

FXFF903 Cut Sheet



Wenglor weFlux2 water flow sensor, thermal, 200mm probe length, 10–400 cm/sec, -25 to +150 °C, Output: analog, Output 2: analog, 12-32 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/FXFF903>

Technical Specifications

Brand	Wenglor
Item	Flow sensor
Series	WeFlux2
Media Type	Water
Sensing Type	Thermal
Probe Length	200mm
Probe Diameter	6mm
Measuring Range	10–400 cm/sec
Measuring Range 2	-25 to +150 °C

Output	Analog, 4–20 mA
Output 2	Analog, 4–20 mA
Operating Voltage	12-32 VDC
Electrical Connection	4-pin M12 quick-disconnect
Wetted Parts	316L stainless steel
IP Rating	IP68 and IP69K
Application	Food and beverage
Additional Information	Purchase cable and mounting fitting separately

Agency Approvals

UL Listed File #	E365080
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/FXFF903.pdf>
See store item page for other formats.