


# G25-SL1000-4LB Cut Sheet



ProSense mechanical pressure gauge, 2.5in diameter, 0 to 1000 psig/0 to 7000 kPa, stainless steel liquid filled case, brass wetted parts, 1/4in male NPT process connection, lower mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/G25-SL1000-4LB>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Mechanical pressure gauge
<b>Diameter</b>	2.5in
<b>Scale</b>	0 to 1000 psig/0 to 7000 kPa
<b>Case Type</b>	Stainless steel liquid filled
<b>Wetted Parts</b>	Brass
<b>Process Connection</b>	1/4in male NPT
<b>Mounting</b>	Lower

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/G25-SL1000-4LB.pdf>  
See store item page for other formats.