

G25-SL30-4CB Cut Sheet



ProSense mechanical pressure gauge, 2.5in diameter, 0 to 30 psig/0 to 210 kPa, stainless steel liquid filled case, phosphor bronze, brass wetted parts, 1/4in male NPT process connection, center back mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/G25-SL30-4CB>

Technical Specifications

Brand	ProSense
Item	Mechanical pressure gauge
Media Type	Liquid, air, gases, oil, water and chemicals
Diameter	2.5in
Scale	0 to 30 psig/0 to 210 kPa
Case Type	Stainless steel liquid filled
Wetted Parts	Phosphor bronze, brass
Sensing Element Material	Phosphor bronze
Process Connection	1/4in male NPT
Mounting	Center back

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/G25-SL30-4CB.pdf>
See store item page for other formats.