G3P-060-STAC Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

AutomationDirect (Eaton) molded case circuit breaker, 100 A frame, 60 A, 480 VAC/250 VDC, 3-pole, characteristics, thermal magnetic, 22 kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals and factory installed 120 VAC shunt trip included.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/G3P-060-STAC

Technical Specifications

Brand	AutomationDirect (Eaton)
Item	Circuit breaker
Circuit Breaker Type	Molded case
Circuit Type	Feeder and branch
Current-Limiting	No
Frame Size	100 A
Amperage Rating	60 A
Voltage Rating	480 VAC/250 VDC
Number of Poles	3

Trip Curve	Characteristics
Trip Type	Thermal magnetic
Interrupting Rating	22 kA @ 480 VAC
UL Rating	UL 489 listed
Mounting	Panel
HACR Rated	Yes
Reverse Feed Capable	Yes
Includes	Line and load lug terminals and factory installed 120 VAC shunt trip

Agency Approvals

UL Listed File #	E503708
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	43556
RoHS Status	No
EU REACH	View EU REACH document