

# G3P-100-UVAC Cut Sheet



AutomationDirect (Eaton) molded case circuit breaker, 100A frame, 100A, 480 VAC / 250 VDC, 3-pole, characteristics, thermal magnetic, 22kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals and factory installed 120 VAC undervoltage release included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/G3P-100-UVAC>

## Technical Specifications

<b>Brand</b>	AutomationDirect (Eaton)
<b>Item</b>	Circuit breaker
<b>Circuit Breaker Type</b>	Molded case
<b>Circuit Type</b>	Feeder and branch
<b>Current-Limiting</b>	No
<b>Frame Size</b>	100A frame
<b>Amperage Rating</b>	100A
<b>Voltage Rating</b>	480 VAC / 250 VDC
<b>Number of Poles</b>	3

<b>Trip Curve</b>	Characteristics
<b>Trip Type</b>	Thermal magnetic
<b>Interrupting Rating</b>	22kA @ 480 VAC
<b>UL Rating</b>	UL 489 listed
<b>Mounting</b>	Panel
<b>HACR Rated</b>	Yes
<b>Reverse Feed Capable</b>	Yes
<b>Includes</b>	Line and load lug terminals and factory installed 120 VAC undervoltage release

## Agency Approvals

<b>UL Listed File #</b>	E503708
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	43556
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>