

G575 Cut Sheet



Marathon standard efficiency AC induction motor, general purpose and 4-in-1, 2hp, 1-phase, 115/208-230 VAC, 1800rpm, TEFC, 56HC frame, rolled steel, C-face/removable rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/G575>

Technical Specifications

| | |
|--------------------------|----------------------------|
| Brand | Marathon |
| Item | Motor |
| Efficiency Group | Standard efficiency |
| Efficiency | 80 |
| Voltage Type | AC |
| Motor Type | Induction |
| Motor Application | General purpose and 4-in-1 |
| Horsepower Rating | 2hp |
| Number of Phases | 1 |
| Voltage Rating | 115/208-230 VAC |
| Synchronous Speed | 1800rpm |
| Nameplate RPM | 1725/1425rpm |
| Overload Type | None |
| Enclosure Type | TEFC |
| Shaft Type | Round with square key |

| | |
|---------------------------------|--------------------------------|
| Shaft Diameter | 5/8in |
| Shaft Material | 1144 Stressproof (C-223) steel |
| Motor Frame | 56HC |
| Frame Material | Rolled steel |
| Electrically Reversible | Yes |
| Insulation Class | Class F |
| IP Rating | IP43 |
| Service Factor | 1.0 |
| Integrated Brake | No |
| NEMA Design | Design N |
| Junction Box Orientation | F1 |
| Mounting | C-face/removable rigid base |
| Mounting Orientation | Horizontal |
| Manufacturer Part Number | 056B17F5306 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E49747 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR2025 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |