

# GBV10N Cut Sheet



NITRA pneumatic threaded fitting, bleed valve, nickel-plated brass body, nickel-plated brass threads, #10-32 male UNF.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GBV10N>

## Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Threaded
Fitting Type	Bleed valve
Body Material	Nickel-plated brass
Thread Material	Nickel-plated brass
Fitting Measurement Type	SAE
Connection	#10-32 male UNF
Operating Pressure	125 psi
Operating Temperature	-20 to 160 deg F

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GBV10N.pdf>  
See store item page for other formats.