

GCB100S-2FF30LL Cut Sheet



Gladiator molded case circuit breaker, 100A frame, 30A, 600Y / 480 VAC / 250 VDC, 2-pole, characteristics, fixed thermal/fixed magnetic, 35kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GCB100S-2FF30LL>

Technical Specifications

| | |
|-----------------------------|--------------------------|
| Brand | Gladiator |
| Item | Circuit breaker |
| Circuit Breaker Type | Molded case |
| Circuit Type | Feeder and branch |
| Current-Limiting | No |
| Frame Size | 100A frame |
| Amperage Rating | 30A |
| Voltage Rating | 600Y / 480 VAC / 250 VDC |
| Number of Poles | 2 |

| | |
|-----------------------------|------------------------------|
| Trip Curve | Characteristics |
| Trip Type | Fixed thermal/fixed magnetic |
| Interrupting Rating | 35kA @ 480 VAC |
| UL Rating | UL 489 listed |
| Mounting | Panel |
| HACR Rated | Yes |
| Reverse Feed Capable | Yes |
| Includes | Line and load lug terminals |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E503708 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GCB100S-2FF30LL.pdf>
See store item page for other formats.