



Gladiator molded case circuit breaker, 1200A frame, 1200A, 600 VAC, 3-pole, characteristics, adjustable electronic, 65kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals and terminal covers included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GCB1200H-3ES1200LL>

Technical Specifications

Brand	Gladiator	Trip Curve	Characteristics
Item	Circuit breaker	Trip Type	Adjustable electronic
Circuit Breaker Type	Molded case	Interrupting Rating	65kA @ 480 VAC
Circuit Type	Feeder and branch	UL Rating	UL 489 listed
Current-Limiting	No	Mounting	Panel
Frame Size	1200A frame	HACR Rated	Yes
Amperage Rating	1200A	Reverse Feed Capable	Yes
Voltage Rating	600 VAC	Includes	Line and load lug terminals and terminal covers
Number of Poles	3		

Agency Approvals

UL Listed File #	E503708
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GCB1200H-3ES1200LL.pdf>
See store item page for other formats.