

# GCB1200S-3ES1200LL Cut Sheet



Gladiator molded case circuit breaker, 1200A frame, 1200A, 600 VAC, 3-pole, characteristics, adjustable electronic, 35kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals and terminal covers included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GCB1200S-3ES1200LL>

## Technical Specifications

Brand	Gladiator
Item	Circuit breaker
Circuit Breaker Type	Molded case
Circuit Type	Feeder and branch
Current-Limiting	No
Frame Size	1200A frame
Amperage Rating	1200A
Voltage Rating	600 VAC
Number of Poles	3

Trip Curve	Characteristics
Trip Type	Adjustable electronic
Interrupting Rating	35kA @ 480 VAC
UL Rating	UL 489 listed
Mounting	Panel
HACR Rated	Yes
Reverse Feed Capable	Yes
Includes	Line and load lug terminals and terminal covers

## Agency Approvals

UL Listed File #	E503708
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/GCB1200S-3ES1200LL.pdf>  
See store item page for other formats.