

# GCB600H-3AA600LL Cut Sheet



Gladiator molded case circuit breaker, 600A frame, 600A, 600 VAC / 600 VDC, 3-pole, characteristics, adjustable thermal/ adjustable magnetic, 65kA @ 480 VAC interrupting rating, panel mount. Line and load lug terminals and terminal covers included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GCB600H-3AA600LL>

## Technical Specifications

<b>Brand</b>	Gladiator
<b>Item</b>	Circuit breaker
<b>Circuit Breaker Type</b>	Molded case
<b>Circuit Type</b>	Feeder and branch
<b>Current-Limiting</b>	No
<b>Frame Size</b>	600A frame
<b>Amperage Rating</b>	600A
<b>Voltage Rating</b>	600 VAC / 600 VDC
<b>Number of Poles</b>	3

<b>Trip Curve</b>	Characteristics
<b>Trip Type</b>	Adjustable thermal/adjustable magnetic
<b>Interrupting Rating</b>	65kA @ 480 VAC
<b>UL Rating</b>	UL 489 listed
<b>Mounting</b>	Panel
<b>HACR Rated</b>	Yes
<b>Reverse Feed Capable</b>	Yes
<b>Includes</b>	Line and load lug terminals and terminal covers

## Agency Approvals

<b>UL Listed File #</b>	E503708
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/GCB600H-3AA600LL.pdf>  
See store item page for other formats.