

GCBX3-EHR-N12-GY Cut Sheet



Gladiator rotary handle, pistol, gray, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 1/12. For use with Gladiator 400A to 600A frame MCCBs. Operating mechanism included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GCBX3-EHR-N12-GY>

Technical Specifications

Brand	Gladiator
Item	Handle
Handle Type	Rotary
Handle Style	Pistol
Color	Gray
Mounting	External front
Number Of Positions	2
Lockable Positions	ON-OFF
Defeatable	Yes
NEMA Rating	1/12
Test Function	No
For Use With	Gladiator 400A to 600A frame MCCBs
Includes	Operating mechanism
Requires	Shaft GCBX4-SFT-XX

Agency Approvals

UL Listed File #	E509077
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GCBX3-EHR-N12-GY.pdf>
See store item page for other formats.