

GCX1226-120 Cut Sheet



AutomationDirect pushbutton, IP65, 22mm, twist-to-release, incandescent illuminated, (1) N.C. contact(s), metal base, metal bezel, Operator: red, mushroom, 40mm, round, plastic, 120 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GCX1226-120>

Technical Specifications

Brand	AutomationDirect
Item	Pushbutton
IP Rating	IP65
Barrel Size	22mm
Action	Twist-to-release
Bulb Type	Incandescent illuminated
Contact Type	(1) N.C.
Base Material	Metal

Bezel Material	Metal
Operator Color	Red
Operator Type	Mushroom
Operator Size	40mm
Operator Shape	Round
Operator Material	Plastic
Voltage Rating	120 VAC/VDC
Voltage Regulation	Full voltage

Agency Approvals

UL Listed File #	None
UL Recognized File #	E189258
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GCX1226-120.pdf>
See store item page for other formats.