

# GCX1255-24L Cut Sheet



AutomationDirect selector switch, 22mm, 2-position, maintained, LED illuminated, (1) N.O. contact(s), metal base, metal bezel, Operator: clear, knob, 30mm, round, plastic, 24 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GCX1255-24L>

## Technical Specifications

|                     |                  |
|---------------------|------------------|
| Brand               | AutomationDirect |
| Item                | Selector switch  |
| Barrel Size         | 22mm             |
| IP Rating           | IP65             |
| Number Of Positions | 2                |
| Action              | Maintained       |
| Bulb Type           | LED illuminated  |
| Contact Type        | (1) N.O.         |
| Base Material       | Metal            |

|                    |              |
|--------------------|--------------|
| Bezel Material     | Metal        |
| Operator Color     | Clear        |
| Operator Type      | Knob         |
| Operator Size      | 30mm         |
| Operator Shape     | Round        |
| Operator Material  | Plastic      |
| Voltage Rating     | 24 VAC/VDC   |
| Voltage Regulation | Full voltage |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | E189258                                |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/GCX1255-24L.pdf>  
See store item page for other formats.