


GCX3153-24 Cut Sheet



AutomationDirect pushbutton, IP40, 22mm, momentary, incandescent illuminated, (1) N.O./ (1) N.C. contact(s), plastic base, plastic bezel, Operator: red/green, double headed, 50mm, rectangular, plastic, operator text "(I) and (0)", 24 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GCX3153-24>

Technical Specifications

Brand	AutomationDirect
Item	Pushbutton
IP Rating	IP40
Barrel Size	22mm
Action	Momentary
Bulb Type	Incandescent illuminated
Contact Type	(1) N.O./ (1) N.C.
Base Material	Plastic
Bezel Material	Plastic
Operator Color	Red/green
Operator Type	Double headed
Operator Size	50mm
Operator Shape	Rectangular
Operator Material	Plastic
Operator Legend	(I) and (0)
Voltage Rating	24 VAC/VDC
Voltage Regulation	Full voltage

Agency Approvals

UL Listed File #	e189258
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	66746
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document