

GCX3430 Cut Sheet



AutomationDirect selector switch, IP65, 22mm, 2-position, spring return from right, key removable left position, (1) N.O. contact(s), plastic base, plastic bezel, Operator: black, key, 30mm, round, plastic.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GCX3430>

Technical Specifications

| | |
|-------------------------------|-----------------------------|
| Brand | AutomationDirect |
| Item | Selector switch |
| Barrel Size | 22mm |
| IP Rating | IP65 |
| Number Of Positions | 2 |
| Action | Spring return from right |
| Key Removable Position | Key removable left position |
| Contact Type | (1) N.O. |
| Base Material | Plastic |
| Bezel Material | Plastic |
| Operator Color | Black |
| Operator Type | Key |
| Operator Size | 30mm |
| Operator Shape | Round |
| Operator Material | Plastic |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | e189258 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 66746 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |