

GECP-1CH-6A Cut Sheet



Gladiator electronic circuit protector, GECP series, 6A, 12/24 VDC, 1 channel(s), slow 1 curve, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GECP-1CH-6A>

Technical Specifications

Brand	Gladiator
Item	Circuit protector
Series	GECP
Circuit Breaker Type	Slim
Circuit Type	Supplementary
Current-Limiting	No
Amperage Rating	6A
Input voltage range	10-30 VDC

Output Voltage Range	10-30 VDC
Channels	1
Trip Curve	Slow 1 curve
Trip Type	Electronic
UL Rating	UL 60947
NEC Class 2	No
Mounting	35mm DIN rail
Connection	Spring terminals

Agency Approvals

UL Listed File #	E191072
UL Recognized File #	E530981
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GECP-1CH-6A.pdf>
See store item page for other formats.