

# GFS30-E1C-120A-F Cut Sheet



AcuAMP ground fault sensor, fixed core, 5, 10, or 30 mA selectable trip point, relay, SPDT normally energized, automatic reset output, 120 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GFS30-E1C-120A-F>

## Technical Specifications

Brand	AcuAMP
Item	Ground fault sensor
Body Type	Fixed core
Trip Point	5, 10, or 30 mA selectable
Output	Relay, SPDT normally energized, automatic reset
Output Rating	1A @ 125VAC, 2A @ 30VDC
Operating Voltage	120 VAC
Mounting	Panel or optional 35mm DIN rail
Electrical Connection	Screw terminals
UL Rating	UL 1053 recognized

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E343037
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>