

GFS30-M1A-24-F Cut Sheet



AcuAMP ground fault sensor, fixed core, 5, 10, or 30 mA selectable trip point, relay, SPST-N.O., manual reset output, 24 VAC/VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GFS30-M1A-24-F>

Technical Specifications

Brand	AcuAMP
Item	Ground fault sensor
Body Type	Fixed core
Trip Point	5, 10, or 30 mA selectable
Output	Relay, SPST-N.O., manual reset
Output Rating	1A @ 125 VAC, 2A @ 30 VDC
Operating Voltage	24 VAC/VDC
Mounting	Panel or optional 35mm DIN rail
Electrical Connection	Screw terminals
UL Rating	UL 1053 recognized

Agency Approvals

UL Listed File #	None
UL Recognized File #	E343037
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GFS30-M1A-24-F.pdf>
See store item page for other formats.