

GFSL30-E1C-24-F Cut Sheet



AcuAMP ground fault sensor, large aperture fixed core, 5, 10, or 30 mA selectable trip point, relay, SPDT normally energized, automatic reset output, 24 VAC/VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GFSL30-E1C-24-F>

Technical Specifications

Brand	AcuAMP
Item	Ground fault sensor
Body Type	Large aperture fixed core
Trip Point	5, 10, or 30 mA selectable
Output	Relay, SPDT normally energized, automatic reset
Output Rating	1A @ 120 VAC, 2A @ 30 VDC
Operating Voltage	24 VAC/VDC
Mounting	Panel or optional 35mm DIN rail
Electrical Connection	Screw terminals
UL Rating	UL 508 listed

Agency Approvals

UL Listed File #	E222847
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GFSL30-E1C-24-F.pdf>
See store item page for other formats.