

GFSL30-M1A-120A-F Cut Sheet



AcuAMP ground fault sensor, large aperture fixed core, 5, 10, or 30 mA selectable trip point, relay, SPST-N.O., manual reset output, 120 VAC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GFSL30-M1A-120A-F>

Technical Specifications

Brand	AcuAMP
Item	Ground fault sensor
Body Type	Large aperture fixed core
Trip Point	5, 10, or 30 mA selectable
Output	Relay, SPST-N.O., manual reset
Output Rating	1A @ 125VAC, 2A @ 30VDC
Operating Voltage	120 VAC
Mounting	Panel or optional 35mm DIN rail
Electrical Connection	Screw terminals
UL Rating	UL 508 listed

Agency Approvals

UL Listed File #	E222847
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document