

# GH15BN-3-10A Cut Sheet



AutomationDirect GH15 series IEC contactor, 9A, (3) N.O. power poles, (1) N.O. auxiliary contacts, 120 VAC (60Hz)/110 VAC (50Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GH15BN-3-10A>

## Technical Specifications

Brand	AutomationDirect
Item	Contactor
Series	GH15
Contactor Type	IEC
Actuator Type	Magnetic
Amperage Rating	9A
Power Poles	(3) N.O.
Auxiliary Contacts	(1) N.O.
Coil Voltage	120 VAC (60Hz)/110 VAC (50Hz)

## Agency Approvals

UL Listed File #	E191059
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GH15BN-3-10A.pdf>  
See store item page for other formats.