

# GH15FT-3-00A Cut Sheet



AutomationDirect GH15 series IEC contactor, 32A, (3) N.O. power poles, 120 VAC (60Hz)/110 VAC (50Hz) coil voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GH15FT-3-00A>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Contactor
<b>Series</b>	GH15
<b>Contactor Type</b>	IEC
<b>Actuator Type</b>	Magnetic
<b>Amperage Rating</b>	32A
<b>Power Poles</b>	(3) N.O.
<b>Coil Voltage</b>	120 VAC (60Hz)/110 VAC (50Hz)

## Agency Approvals

<b>UL Listed File #</b>	E191059
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GH15FT-3-00A.pdf>  
See store item page for other formats.