

GHSE19-013A-02-10S Cut Sheet

Alliance Sensors inductive linear position sensor, spring loaded slide, 13mm stroke, 0-10 VDC output, 19mm diameter x 88.9mm body, 1/2-20 UNF mount, 6-pin PT0.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GHSE19-013A-02-10S>

Technical Specifications

Brand	Alliance Sensors
Item	Linear position sensor
Transducer Type	Inductive
Action	Spring loaded slide
Stroke	13mm
Output	0-10 VDC
Head Type	AGD #9 contact tip
Head Material	Hardened steel
Housing Material	Stainless steel
Housing Size	19mm diameter x 88.9mm body
Operating Voltage	12-30 VDC
Sensor Resolution	0.025% of full scale
Linearity	+/- 0.15%
Switching Cycles	250,000,000 cycles
Mounting	1/2-20 UNF
IP Rating	IP67
Connection	6-pin PT0
Includes	Mounting hardware
Additional Information	Contactless operation

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document