

GIB-Z-360-V-2A Cut Sheet



Gefran inclination sensor, 1 axis, +/- 180 degrees, +/-0.5 degrees accuracy, 0-10 VDC output, IP67 IP69K, thermoplastic (PBT) housing, pigtail, 6.5ft/2m cable length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GIB-Z-360-V-2A>

Technical Specifications

Brand	Gefran
Item	Inclination sensor
Number of Axes	1
Measuring Range	+/- 180 degrees
Accuracy	+/-0.5 degrees
Output	0-10 VDC
Operating Voltage	10-36 VDC
IP Rating	IP67 IP69K
Housing Material	Thermoplastic (PBT)
Connection	Pigtail
Cable Length	6.5ft/2m
Number of Wires	3
Conductor Size	22 AWG
Jacket Material	PUR

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document