

# GIG-Z-360-A-M12 Cut Sheet



Gefran inclination sensor, 1 axis, +/- 180 degrees, +/-0.5 degrees accuracy, redundant 4-20 mA output, IP67, thermoplastic (PBT) housing, (2) 5-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GIG-Z-360-A-M12>

## Technical Specifications

Brand	Gefran
Item	Inclination sensor
Number of Axes	1
Measuring Range	+/- 180 degrees
Accuracy	+/-0.5 degrees
Output	Redundant 4-20 mA
Operating Voltage	10-36 VDC
IP Rating	IP67
Housing Material	Thermoplastic (PBT)
Connection	(2) 5-pin M12 quick-disconnect
Number of Wires	3
Additional Information	Purchase cable separately

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/GIG-Z-360-A-M12.pdf>  
See store item page for other formats.