

GLHD-SS-145002-BS Cut Sheet



IDEM safety switch, cable-pull interlock, with reset, 250m maximum pull cable length, emergency stop, dual head, (4) N.C. safety output(s), (2) N.O. monitoring output(s), 110 VAC LED, 316 stainless steel body, (4) 1/2in NPT cable entries.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GLHD-SS-145002-BS>

Technical Specifications

Brand	IDEM
Item	Safety switch
Actuator Type	Cable-pull interlock
Reset	Yes
Head Type	Dual
Action	Snap acting switch mechanism
Maximum Pull Cable Length	250m
Emergency Stop	Yes

Safety Output Type	(4) N.C.
Monitoring Output Type	(2) N.O.
Indicating Type	110 VAC LED
Housing Size	327 x 110 x 60mm
Body Material	316 stainless steel
IP Rating	IP67 IP69K
Connection	(4) 1/2in NPT cable entries
Includes	(1) tamper-proof T20 Torx bit

Agency Approvals

UL Listed File #	E258676
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GLHD-SS-145002-BS.pdf>
See store item page for other formats.