

GLHR-141302-Z Cut Sheet



IDEM Z-Range safety switch, cable-pull interlock, 125m maximum pull cable length, emergency stop, right hand head, (2) OSSD safety output(s), (1) status monitoring output(s), dual color LED, die-cast aluminum body, 8-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GLHR-141302-Z>

Technical Specifications

Brand	IDEM
Series	Z-Range
Item	Safety switch
Actuator Type	Cable-pull interlock
Reset	Yes
Head Type	Right hand
Maximum Pull Cable Length	125m
Emergency Stop	Yes
Safety Output Type	(2) OSSD

Monitoring Output Type	(1) status
Indicating Type	Dual color LED
Housing Size	223 x 110 x 60mm
Body Material	Die-cast aluminum
IP Rating	IP67
Connection	8-pin M12 quick-disconnect
Cable Length	9.8in/250mm
Includes	(1) tamper-proof T20 Torx bit

Agency Approvals

UL Listed File #	E258676
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GLHR-141302-Z.pdf>
See store item page for other formats.