

GM-312 Cut Sheet



NITRA pneumatic valve manifold, anodized aluminum, white, rectangular, (2) stations, #10-32 female UNF inlet(s), #10-32 female UNF outlet(s), #10-32 female threaded exhaust(s). For use with GVP-21 and GVP-31 series solenoid valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GM-312>

Technical Specifications

Brand	NITRA
Item	Valve manifold
Working Fluid	Air or inert gas
Material	Anodized aluminum
Color	White
Shape	Rectangular
Number of Stations	2
Inlet Port	#10-32 female UNF
Outlet Port	#10-32 female UNF
Exhaust Port	#10-32 female threaded
For Use With	GVP-21 and GVP-31 series solenoid valves

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GM-312.pdf>
See store item page for other formats.