


GM-312 Cut Sheet



NITRA pneumatic valve manifold, anodized aluminum, rectangular, (2) stations, #10-32 female threaded inlet(s), #10-32 female threaded outlet(s), #10-32 female threaded exhaust(s). For use with GVP-21 and GVP-31 series solenoid valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GM-312>

Technical Specifications

Brand	NITRA
Item	Pneumatic Valve manifold
Material	Anodized aluminum
Shape	Rectangular
Number of Stations	2
Inlet Port	#10-32 female threaded
Outlet Port	#10-32 female threaded
Exhaust Port	#10-32 female threaded
For Use With	GVP-21 and GVP-31 series solenoid valves

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document
Other	None