

# GM-314 Cut Sheet



NITRA pneumatic valve manifold, anodized aluminum, white, rectangular, (4) stations, #10-32 female UNF inlet(s), #10-32 female UNF outlet(s), #10-32 female threaded exhaust(s). For use with GVP-21 and GVP-31 series solenoid valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GM-314>

## Technical Specifications

Brand	NITRA
Item	Valve manifold
Working Fluid	Air or inert gas
Material	Anodized aluminum
Color	White
Shape	Rectangular
Number of Stations	4
Inlet Port	#10-32 female UNF
Outlet Port	#10-32 female UNF
Exhaust Port	#10-32 female threaded
For Use With	GVP-21 and GVP-31 series solenoid valves

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GM-314.pdf>  
See store item page for other formats.