

GMA-25 Cut Sheet



Bussmann fuse, GMA series, small dimension, fast-acting, 0.25A, 250 VAC, glass tube. Package of 5. Supplemental, electronic protection applications. Manufacturer part number: GMA-250-R.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GMA-25>

Technical Specifications

| | |
|--------------------------|--|
| Brand | Bussmann |
| Item | Fuse |
| Series | GMA |
| Fuse Class | Small dimension |
| Curve Characteristics | Fast-acting |
| Amperage Rating | 0.25A |
| Voltage Rating | 250 VAC |
| Body Type | Glass tube |
| Size | 5x20mm or 0.2x0.79in |
| Quantity per Pack | 5 |
| Application | Supplemental, electronic protection applications |
| Manufacturer Part Number | GMA-250-R |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E19180 |
| UL Recognized File # | E19180 |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 227483 |
| RoHS Status | No |
| EU REACH | View EU REACH document |
| Other | None |