

GMCB-1B-10 Cut Sheet



Gladiator miniature supplementary protector, 10A, 277 VAC / 60 VDC, 1-pole, B curve, thermal magnetic, 6kA @ 277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GMCB-1B-10>

Technical Specifications

| | |
|----------------------|-------------------------|
| Brand | Gladiator |
| Item | Supplementary protector |
| Circuit Breaker Type | Miniature |
| Circuit Type | Supplementary |
| Current-Limiting | No |
| Amperage Rating | 10A |
| Voltage Rating | 277 VAC / 60 VDC |
| Number of Poles | 1 |
| Trip Curve | B curve |
| Trip Type | Thermal magnetic |
| Interrupting Rating | 6kA @ 277 VAC |
| UL Rating | UL 1077 recognized |
| Mounting | 35mm DIN rail |
| HACR Rated | No |
| Reverse Feed Capable | No |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E508820 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |