

# GMCB-1B-2 Cut Sheet



Gladiator miniature supplementary protector, 2A, 277 VAC / 60 VDC, 1-pole, B curve, thermal magnetic, 6kA @ 277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GMCB-1B-2>

## Technical Specifications

Brand	Gladiator
Item	Supplementary protector
Circuit Breaker Type	Miniature
Circuit Type	Supplementary
Current-Limiting	No
Amperage Rating	2A
Voltage Rating	277 VAC / 60 VDC
Number of Poles	1

Trip Curve	B curve
Trip Type	Thermal magnetic
Interrupting Rating	6kA @ 277 VAC
UL Rating	UL 1077 recognized
Mounting	35mm DIN rail
HACR Rated	No
Reverse Feed Capable	No

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E508820
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GMCB-1B-2.pdf>  
See store item page for other formats.