

# GMCB-1D-30 Cut Sheet



Gladiator miniature supplementary protector, 30A, 277 VAC / 60 VDC, 1-pole, D curve, thermal magnetic, 6kA @ 277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GMCB-1D-30>

## Technical Specifications

<b>Brand</b>	Gladiator
<b>Item</b>	Supplementary protector
<b>Circuit Breaker Type</b>	Miniature
<b>Circuit Type</b>	Supplementary
<b>Current-Limiting</b>	No
<b>Amperage Rating</b>	30A
<b>Voltage Rating</b>	277 VAC / 60 VDC
<b>Number of Poles</b>	1
<b>Trip Curve</b>	D curve
<b>Trip Type</b>	Thermal magnetic
<b>Interrupting Rating</b>	6kA @ 277 VAC
<b>UL Rating</b>	UL 1077 recognized
<b>Mounting</b>	35mm DIN rail
<b>HACR Rated</b>	No
<b>Reverse Feed Capable</b>	No

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E508820
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>