

# GMCBU-1B-63 Cut Sheet



Gladiator miniature circuit breaker, 63A, 240 VAC / 60 VDC, 1-pole, B curve, thermal magnetic, 10kA @ 120/240 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GMCBU-1B-63>

## Technical Specifications

|                      |                   |
|----------------------|-------------------|
| Brand                | Gladiator         |
| Item                 | Circuit breaker   |
| Circuit Breaker Type | Miniature         |
| Circuit Type         | Feeder and branch |
| Current-Limiting     | No                |
| Amperage Rating      | 63A               |
| Voltage Rating       | 240 VAC / 60 VDC  |
| Number of Poles      | 1                 |

|                      |                    |
|----------------------|--------------------|
| Trip Curve           | B curve            |
| Trip Type            | Thermal magnetic   |
| Interrupting Rating  | 10kA @ 120/240 VAC |
| UL Rating            | UL 489 listed      |
| Mounting             | 35mm DIN rail      |
| HACR Rated           | Yes                |
| Reverse Feed Capable | Yes                |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E503708                                |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GMCBU-1B-63.pdf>  
See store item page for other formats.