

GMCBU-2C-16 Cut Sheet



Gladiator miniature circuit breaker, 16A, 480Y / 277 VAC / 125 VDC, 2-pole, C curve, thermal magnetic, 10kA @ 480Y/277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GMCBU-2C-16>

Technical Specifications

Brand	Gladiator
Item	Circuit breaker
Circuit Breaker Type	Miniature
Circuit Type	Feeder and branch
Current-Limiting	No
Amperage Rating	16A
Voltage Rating	480Y / 277 VAC / 125 VDC
Number of Poles	2
Trip Curve	C curve
Trip Type	Thermal magnetic
Interrupting Rating	10kA @ 480Y/277 VAC
UL Rating	UL 489 listed
Mounting	35mm DIN rail
HACR Rated	Yes
Reverse Feed Capable	Yes

Agency Approvals

UL Listed File #	E503708
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document