

GMCBU-3B-16 Cut Sheet



Gladiator miniature circuit breaker, 16A, 480Y / 277 VAC / 125 VDC, 3-pole, B curve, thermal magnetic, 10kA @ 480Y/277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GMCBU-3B-16>

Technical Specifications

| | |
|----------------------|--------------------------|
| Brand | Gladiator |
| Item | Circuit breaker |
| Circuit Breaker Type | Miniature |
| Circuit Type | Feeder and branch |
| Current-Limiting | No |
| Amperage Rating | 16A |
| Voltage Rating | 480Y / 277 VAC / 125 VDC |
| Number of Poles | 3 |

| | |
|----------------------|---------------------|
| Trip Curve | B curve |
| Trip Type | Thermal magnetic |
| Interrupting Rating | 10kA @ 480Y/277 VAC |
| UL Rating | UL 489 listed |
| Mounting | 35mm DIN rail |
| HACR Rated | Yes |
| Reverse Feed Capable | Yes |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E503708 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GMCBU-3B-16.pdf>
See store item page for other formats.