

# GMCBU-3B-3 Cut Sheet



Gladiator miniature circuit breaker, 3A, 480Y / 277 VAC / 125 VDC, 3-pole, B curve, thermal magnetic, 10kA @ 480Y/277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GMCBU-3B-3>

## Technical Specifications

|                             |                          |
|-----------------------------|--------------------------|
| <b>Brand</b>                | Gladiator                |
| <b>Item</b>                 | Circuit breaker          |
| <b>Circuit Breaker Type</b> | Miniature                |
| <b>Circuit Type</b>         | Feeder and branch        |
| <b>Current-Limiting</b>     | No                       |
| <b>Amperage Rating</b>      | 3A                       |
| <b>Voltage Rating</b>       | 480Y / 277 VAC / 125 VDC |
| <b>Number of Poles</b>      | 3                        |
| <b>Trip Curve</b>           | B curve                  |
| <b>Trip Type</b>            | Thermal magnetic         |
| <b>Interrupting Rating</b>  | 10kA @ 480Y/277 VAC      |
| <b>UL Rating</b>            | UL 489 listed            |
| <b>Mounting</b>             | 35mm DIN rail            |
| <b>HACR Rated</b>           | Yes                      |
| <b>Reverse Feed Capable</b> | Yes                      |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E503708                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |