

# GMCBU-3C-32 Cut Sheet



Gladiator miniature circuit breaker, 32A, 240 VAC / 125 VDC, 3-pole, C curve, thermal magnetic, 10kA @ 240 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GMCBU-3C-32>

## Technical Specifications

|                      |                   |
|----------------------|-------------------|
| Brand                | Gladiator         |
| Item                 | Circuit breaker   |
| Circuit Breaker Type | Miniature         |
| Circuit Type         | Feeder and branch |
| Current-Limiting     | No                |
| Amperage Rating      | 32A               |
| Voltage Rating       | 240 VAC / 125 VDC |
| Number of Poles      | 3                 |

|                      |                  |
|----------------------|------------------|
| Trip Curve           | C curve          |
| Trip Type            | Thermal magnetic |
| Interrupting Rating  | 10kA @ 240 VAC   |
| UL Rating            | UL 489 listed    |
| Mounting             | 35mm DIN rail    |
| HACR Rated           | Yes              |
| Reverse Feed Capable | Yes              |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E503708                                |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GMCBU-3C-32.pdf>  
See store item page for other formats.