

GMCBU-3D-25 Cut Sheet



Gladiator miniature circuit breaker, 25A, 480Y / 277 VAC / 125 VDC, 3-pole, D curve, thermal magnetic, 10kA @ 480Y/277 VAC interrupting rating, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GMCBU-3D-25>

Technical Specifications

Brand	Gladiator
Item	Circuit breaker
Circuit Breaker Type	Miniature
Circuit Type	Feeder and branch
Current-Limiting	No
Amperage Rating	25A
Voltage Rating	480Y / 277 VAC / 125 VDC
Number of Poles	3

Trip Curve	D curve
Trip Type	Thermal magnetic
Interrupting Rating	10kA @ 480Y/277 VAC
UL Rating	UL 489 listed
Mounting	35mm DIN rail
HACR Rated	Yes
Reverse Feed Capable	Yes

Agency Approvals

UL Listed File #	E503708
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GMCBU-3D-25.pdf>
See store item page for other formats.