

# GP2E05 Cut Sheet



Schneider Electric Easy TeSys series manual motor protector, pushbutton, 1A, thermal overload, 0.63-1 adjustable, 13A instantaneous trip rating, 45mm frame.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GP2E05>

## Technical Specifications

<b>Brand</b>	Schneider Electric
<b>Series</b>	Easy TeSys
<b>Item</b>	Motor protector
<b>Starter Type</b>	Manual
<b>Actuator Type</b>	Pushbutton
<b>Amperage Rating</b>	1A
<b>Voltage Rating</b>	600 VAC
<b>Relay Type</b>	Thermal overload
<b>Operation Type</b>	Bi-metallic
<b>Full Load Amperage Range</b>	0.63-1 adjustable
<b>Instantaneous Trip Rating</b>	13A

<b>Number of Poles</b>	3
<b>Power Poles</b>	(3) N.O.
<b>Trip Class</b>	Trip Class 10
<b>Phase Loss Sensitive</b>	Yes
<b>Ground Fault Protection</b>	No
<b>SCCR Rating</b>	35kA SCCR
<b>UL Rating</b>	UL 60947-4-1
<b>Frame</b>	45mm
<b>Mounting</b>	35mm DIN rail
<b>Connection</b>	Screw terminal

## Agency Approvals

<b>UL Listed File #</b>	E89451
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	164581
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/GP2E05.pdf>  
See store item page for other formats.